

PROCLEAR® MULTIFOCAL

EXCELLENT HEALTH AND ALL-DAY COMFORT
FOR YOUR PRESBYOPIC PATIENTS

XR RANGE
Now Available
at Wal-Mart and
Sam's Club



Proclear Multifocal has a proven track record of providing outstanding vision, health, and comfort. Now with the addition of an XR range, offering sphere powers up to +/- 20.00D, and ADDs up to +4.00D, even more of your presbyopic patients can enjoy the benefits of Proclear Multifocal.

BALANCED PROGRESSIVE™ TECHNOLOGY— two different, complementary lenses work together to provide exceptional vision at all distances.

PC TECHNOLOGY™ leads to a more comfortable lens-wearing experience—especially important to presbyopic patients whose eyes often grow drier as they age.

SEVEN AVAILABLE ADD POWERS let you more easily fit your presbyopic patients as their condition progresses, offering superior patient retention.



PARAMETERS	MATERIAL	WEARING SCHEDULE	WATER CONTENT	BASE CURVE (mm)	DIAMETER (mm)	SPHERE POWER	ADD POWER	LENS DESIGN	HANDLING TINT	LENS CARE	MODALITY
PROCLEAR MULTIFOCAL	omafilcon A	Daily wear	62%	8.7	14.4	+4.00D to -6.00D (in 0.25D steps)	+1.00 +1.50 +2.00 +2.50	D lens N lens	Light blue	Chemical or peroxide disinfection	Monthly replacement
PROCLEAR MULTIFOCAL XR†	omafilcon A	Daily wear	59%	8.7	14.4	+4.25D to +20.00D, -6.25D to -20.00D (0.50D steps after +/- 6.50D)	+1.00 +1.50 +2.00 +2.50	D lens N lens	Light blue	Chemical or peroxide disinfection	Monthly replacement
					+20.00D to -20.00D (0.50D steps after +/- 6.50D)	+3.00 +3.50 +4.00					

†Proclear Multifocal XR is a made-to-order lens and will ship within 10 days from the time of your order.



SEE BEYOND THE ORDINARY®

coopervision.com | 800-341-2020